

Garant

eco grooving tool strengthened, right-hand, Blade height h₅ / groove width w: 26/3Lmm

**Order data**

Order number	273854 26/3L
GTIN	4045197989178
Item class	21W

Description**Version:**

With eco cooling directly to the cutting edge and additional rake face cooling.
With coolant transfer for toolholders from other manufacturers.

Attention:

Please order the assembly key No. 279920 separately.

Note:

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149.
Please order the assembly key No. 279920 separately. From 19.5 mm groove depth onwards the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

Technical description

Height h ₁	21.4 mm
for maximum workpiece Ø	90 mm
Blade height h ₅	26 mm
Series	Eco
Overall length L	96 mm
Application type	right-hand
Through-coolant	yes

axial grooving possible	no
Type of product	Parting-off tool