

Garant

eco grooving tool strengthened, right-hand, Blade height h5 / groove width w: 32/3Lmm


Order data

| | |
|--------------|---------------|
| Order number | 273854 32/3L |
| GTIN | 4045197989314 |
| Item class | 21W |

Description
Version:

With eco cooling directly to the cutting edge and additional rake face cooling.
With coolant transfer for toolholders from other manufacturers.

Attention:

Please order the assembly key No. 279920 separately.

Note:

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149.
Please order the assembly key No. 279920 separately. From 19.5 mm groove depth onwards the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

Technical description

| | |
|-------------------------------------|------------|
| for maximum workpiece \varnothing | 90 mm |
| Height h_1 | 25 mm |
| Blade height h_5 | 32 mm |
| Series | Eco |
| Overall length L | 100 mm |
| Application type | right-hand |
| Through-coolant | yes |

| | |
|-------------------------|------------------|
| axial grooving possible | no |
| Type of product | Parting-off tool |