

**Garant**

**eco grooving tool strengthened, left-hand, Blade height h<sub>5</sub> / groove width w: 32/3Lmm**


**Order data**

Order number	273855 32/3L
GTIN	4045197989321
Item class	21W

**Description**
**Version:**

With eco cooling directly to the cutting edge and additional rake face cooling.  
With coolant transfer for toolholders from other manufacturers.

**Attention:**

Please order the assembly key No. 279920 separately.

**Note:**

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149.  
Please order the assembly key No. 279920 separately. From 19.5 mm groove depth onwards the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

**Technical description**

Blade height h <sub>5</sub>	32 mm
for maximum workpiece Ø	90 mm
Series	Eco
Height h <sub>1</sub>	25 mm
Overall length L	100 mm
Application type	left-hand
Through-coolant	yes
axial grooving possible	no

Type of product

Parting-off tool