

## Workplace mat , 100 % natural rubber, black



### Order data

Order number	964565
GTIN	662641017634
Item class	96C

### Description

#### Version:

100% natural rubber, **not oil-resistant** (if continuously exposed to oil).

#### Description:

- **Industrial workplace mat with sealed non-slip surface.**
- **19 mm thick material offers high ergonomic benefits and anti-fatiguing effect.**
- **Flexible interlocking system tiles 91×91 cm, permits optimum adaptation to local conditions.**
- **Flexible edging allows creation of internal and external corners.**
- **Non-slip characteristics R9 to DIN 51130 and BGR 181. Of virtually indestructible rubber.**
- **Silicone-free, therefore suitable for paint shops. Resistant to most chemicals and to extreme temperatures.**

#### Note:

Suitable edge strips under No. 964577 and 964578 each size 0 and 1.

Please ensure good ventilation during heavy exposure to sparks.

### Technical description

with safety edges	can be extended
plug-in	yes
Surface	Anti-slip surface
Weight	12.7 kg
Thickness	19 mm

Width	91 cm
Length	91 cm
Material	Natural rubber
silicone-free	yes
Non-slip characteristics to DIN 51130, BGR 181	R9
Manufacturer's designation	Cushion Ease Solid™
Standing in comfort	Insulation (temperature)
Standing in comfort	Anti-slip
Standing in comfort	Anti-fatiguing
Shock protection	Floor
Material characteristics	not oil-resistant
Colour	black
Type of product	Workplace mat