

**Profile tray galvanized, Number of drums×drum content (l) / Type: 2X200****Order data**

Order number	984000 2X200
GTIN	4052462022911
Item class	96U

**Description****Version:**

Of 2 mm sheet metal. Access height 100 mm. Profiles as base. Stackable.

Hot-dip galvanised to EN ISO 1461.

**Application:**

For storage and discharge of 200 litre drums. Can also be combined with 60 litre drums. For flammable liquids of GHS categories 1 – 4 and for water-polluting liquids of GHS categories 1 – 4.

**Note:**

**Not approved for Germany (export version).** No declaration of conformity (ÜHP) according to Building Regulations List A, part 1, DIBt, Berlin. **Please refer to the regulations applicable in your country.**

Storage: Storage of flammable substances permitted

Drip catch volume: 245 l

Height: 360 mm

Width: 1200 mm

Depth: 800 mm

Storage capacity 200 litre drums: 2

Load capacity: 480 kg

**Technical description**

Weight	52 kg
Height	360 mm
Drum contents	200 l
Storage capacity 200 litre drums	2
Depth	800 mm
Number of drums	2
Width	1200 mm
Drip catch volume	245 l
Load capacity	480 kg
Material thickness	2 mm
Storage	Storage of environmentally polluting substances
Storage	Storage of flammable substances permitted
Type of product	Drip tray