

Profile tray galvanized, Number of drums×drum content (l) / Type: 4X200**Order data**

Order number	984000 4X200
GTIN	4052462022966
Item class	96U

Description**Version:**

Of 2 mm sheet metal. Access height 100 mm. Profiles as base. Stackable.
Hot-dip galvanised to EN ISO 1461.

Application:

For storage and discharge of 200 litre drums. Can also be combined with 60 litre drums. For flammable liquids of GHS categories 1 – 4 and for water-polluting liquids of GHS categories 1 – 4.

Note:

Not approved for Germany (export version). No declaration of conformity (ÜHP) according to Building Regulations List A, part 1, DIBt, Berlin. **Please refer to the regulations applicable in your country.**

Storage: Storage of flammable substances permitted

Drip catch volume: 261 l

Height: 285 mm

Width: 1200 mm

Depth: 1200 mm

Storage capacity 200 litre drums: 4

Load capacity: 960 kg

Technical description

Depth	1200 mm
Drum contents	200 l
Height	285 mm
Number of drums	4
Width	1200 mm
Drip catch volume	261 l
Storage capacity 200 litre drums	4
Weight	63 kg
Load capacity	960 kg
Material thickness	2 mm
Storage	Storage of environmentally polluting substances
Storage	Storage of flammable substances permitted
Type of product	Drip tray