

Workplace mat , 100 % nitrile rubber oil-resistant, black



Order data

Order number	964566
GTIN	662641769168
Item class	96C

Description

Version:

100% nitrile rubber, **oil-resistant**.

Description:

- **Industrial workplace mat with sealed non-slip surface.**
- **19 mm thick material offers high ergonomic benefits and anti-fatiguing effect.**
- **Flexible interlocking system tiles 91×91 cm, permits optimum adaptation to local conditions.**
- **Flexible edging allows creation of internal and external corners.**
- **Non-slip characteristics R9 to DIN 51130 and BGR 181. Of virtually indestructible rubber.**
- **Silicone-free, therefore suitable for paint shops. Resistant to most chemicals and to extreme temperatures.**

Suitable for :

Edge strips No. 964577 and No. 964578 each size 0 and 1.

Note:

Please ensure good ventilation during heavy exposure to sparks.

Material characteristics: oil-resistant

Length: 91 cm

Width: 91 cm

Thickness: 19 mm

Weight: 12.7 kg

Technical description

Thickness	19 mm
-----------	-------

silicone-free	yes
Surface	Anti-slip surface
with safety edges	can be extended
plug-in	yes
Material	Nitrile rubber
Weight	12.7 kg
Width	91 cm
Length	91 cm
Non-slip characteristics to DIN 51130, BGR 181	R9
Manufacturer's designation	Cushion Ease Solid™ Nitrile
Standing in comfort	Insulation (temperature)
Standing in comfort	Anti-slip
Standing in comfort	Anti-fatiguing
Shock protection	Floor
Material characteristics	oil-resistant
Colour	black
Type of product	Workplace mat