

## Workplace mat , 100 % nitrile rubber flame resistant, black



### Order data

Order number	964567
GTIN	662641780248
Item class	96C

### Description

#### Version:

100 % nitrile rubber mixture, **oil-resistant**.

**Flame resistant** (suitable for fabrication shops).

Tested for flame resistance class Bfl-S1 to DIN EN 13501 and class 1 to ASTM E648-03 (NFPA253).

#### Description:

- **Industrial workplace mat with sealed non-slip surface.**
- **19 mm thick material offers high ergonomic benefits and anti-fatiguing effect.**
- **Flexible interlocking system tiles 91×91 cm, permits optimum adaptation to local conditions.**
- **Flexible edging allows creation of internal and external corners.**
- **Non-slip characteristics R9 to DIN 51130 and BGR 181. Of virtually indestructible rubber.**
- **Silicone-free, therefore suitable for paint shops. Resistant to most chemicals and to extreme temperatures.**

#### Note:

Suitable edge strips under No. 964577 and 964578 each size 0 and 1.

Please ensure good ventilation during heavy exposure to sparks.

### Technical description

Width	91 cm
plug-in	yes
Thickness	19 mm

silicone-free	yes
Material	Nitrile rubber
Surface	Anti-slip surface
Length	91 cm
Weight	12.7 kg
with safety edges	can be extended
Non-slip characteristics to DIN 51130, BGR 181	R9
Manufacturer's designation	Cushion Ease Solid™ Nitrile FR
Standing in comfort	Anti-slip
Standing in comfort	Insulation (temperature)
Standing in comfort	Anti-fatiguing
Shock protection	Floor
Material characteristics	oil-resistant
Material characteristics	flame resistant
Colour	black
Type of product	Workplace mat