

**Wide-span add-on rack, Depth 1000 mm, Height / Shelf width: 3000/2500mm****Order data**

Order number	990975 3000/2500
GTIN	4004514226297
Item class	960

**Description****Version:**

Framework galvanised. Optionally galvanised 25 mm steel panels or chipboard. Different types of cross beam depending on the required load per shelf (cross piece height 55 – 85 mm). Quick assembly by simply plugging in the type ZG cross beams. **Shelf loading** maximum 1050 kg, **bay loading** maximum 3500 kg.

**Description:****Assembled size:**

Nominal length + number of stiles × 57 mm.

**Application:**

Storage of bulky, awkward, and heavy goods. Deposit and retrieval available from both sides.

**Colour:**

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

**Note:**

- **The free unsupported length (K) must not be more than 1200 mm, but only for a bay load of max. 2600 kg. The permissible bay load must be reduced in recognition of this shelf.**
- **Floor and wall fastenings are not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

**Technical description**

Shelf width	2500 mm
Customer assembly	yes
Material of storage level	Steel panels
Assembled size add-on rack width	2557 mm
Rack installation	Extension rack
Width	2557 mm
Storage shelf depth	1000 mm
Shelf load capacity	820 kg
Height	3000 mm
Number of storage levels steel panels	5
Depth	1000 mm
Rack depth	1000 mm
Rack width	2500 mm
Rack height	3000 mm
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004
Product name attribute	Depth 1000 mm
Type of product	Wide-span racking