

Wide-span basic rack, Depth 1000 mm, Height / Shelf width: 2000/1785mm**Order data**

Order number	990970 2000/1785
GTIN	4004514225818
Item class	960

Description**Version:**

Framework galvanised. Optionally galvanised 25 mm steel panels or chipboard. Different types of cross beam depending on the required load per shelf (cross piece height 55 – 85 mm). Quick assembly by simply plugging in the type ZG cross beams. **Shelf loading** maximum 1050 kg, **bay loading** maximum 3500 kg.

Description:**Assembled size:**

Nominal length + number of stiles × 57 mm.

Application:

Storage of bulky, awkward, and heavy goods. Deposit and retrieval available from both sides.

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **The free unsupported length (K) must not be more than 1200 mm, but only for a bay load of max. 2600 kg. The permissible bay load must be reduced in recognition of this shelf.**
- **Floor and wall fastenings are not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Shelf load capacity	670 kg
Shelf width	1785 mm
Storage shelf depth	1000 mm
Material of storage level	Steel panels
Rack installation	Basic rack
Number of storage levels steel panels	3
Assembled size basic rack width	1899 mm
Height	2000 mm
Customer assembly	yes
Width	1899 mm
Depth	1000 mm
Rack depth	1000 mm
Rack width	1785 mm
Rack height	2000 mm
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004
Product name attribute	Depth 1000 mm
Type of product	Wide-span racking