



Work platform folding, with double-sided access, Number of steps including platform: 2X2



Order data

Order number	966070 2X2
GTIN	4003866403721
Item class	96Z

Description

Version:

Treads and stiles of extruded aluminium profile.

Large platform with integrated hinged connection.

85 mm deep treads with anti-slip grooves and patented 7-point tread-stile connection. Optimum stability due to rigid connections on both sides.

Standard:

DIN EN 14183.

Technical description

Rung/step depth	85 mm
Working height approx.	2.49 m
Number of steps including platform	2x2
Weight	5.7 kg
Platform height without railing	0.49 m

outer width at bottom	0.7 m
Platform depth	300 mm
Platform width	600 mm
Accessibility	double-sided
Type of step	step
Ladders and platforms load capacity	150 kg
Type of product	Work platform