



Stepladder single-sided access, Number of steps including platform: 5



Order data

Order number	966000 5
GTIN	4003866403356
Item class	96Z

Description

Version:

Treads and stiles made of extruded aluminium sections. Large safety platform (380 × 260 mm) with integrated hinged connection, **safety bridge** and wide **shelf**. Treads 85 mm deep with safe, non-slip serrated surfaces and patented 7-point connection between tread and stile. Optimum stability due to rigid connections on both sides. Two integral bucket hooks.

Standard:

DIN EN 131.

Technical description

Type of step	Step
outer width at bottom	0.49 m
Storage tray available	yes
Ladder length	1.9 m
Number of steps including platform	5
Weight	8 kg

Working height approx.	3.1 m
Standard	DIN EN 131-2; TRBS 2121; BGI 694
Material	Steps and stiles made of extruded aluminium sections
Platform height	1.1 m
Cross beam height	87 mm
Rung/step depth	85 mm
Accessibility	single-sided
Ladders and platforms load capacity	150 kg
Type of product	Stepladder