



## Stepladder double-sided access, Number of steps: 2X3



### Order data

Order number	966050 2X3
GTIN	4003866403530
Item class	96Z

### Description

**Version:**

Treads and stiles made of extruded aluminium sections. Large platform with integrated hinged connection. Treads 85 mm deep with safe, non-slip serrated surfaces and patented 7-point connection between tread and stile. Optimum stability due to rigid connections on both sides.

**Standard:**

**DIN EN 131.**

### Technical description

Cross beam height	87 mm
Working height approx.	2.25 m
Weight	4.5 kg
Belt to prevent splay	double-sided, rigid connection
Number of steps	2x3
outer width at bottom	0.41 m

Standard	DIN EN 131-2; TRBS 2121; BGI 694
Material	Steps and stiles made of extruded aluminium sections
Rung/step depth	85 mm
Ladder length	0.74 m
Type of step	Step
Accessibility	double-sided
Ladders and platforms load capacity	150 kg
Type of product	Stepladder