

**Platform steps, Number of steps including platform: 2****Order data**

Order number	966190 2
GTIN	4003866555208
Item class	96Z

**Description****Version:**

Stiles made from high-strength extruded aluminium sections with screw channels for flexible assembly. The scope of supply excludes handrails and platform railings. These are available under No. 966196 and No. 966198. Steps rise angle 45°. Platform length 400 mm. Serrated aluminium tread covering. Fitted with rollers on the support section.

**Standard:**

**DIN EN ISO 14 122**

**Technical description**

Material	Stiles of high-strength extruded aluminium profiles
Platform height without railing	0.4 m
Throat	870 mm
Standard	DIN EN ISO 14 122
Type of step	Step
Number of steps including platform	2
Weight	28.5 kg

Platform length	400 mm
Step inclination	45 degrees
Accessibility	single-sided
Rung/step width	600 mm
Rollers	yes
Ladders and platforms load capacity	300 kg
Product name attribute	Tread width 600 mm
Two hands free principle	yes
Type of product	Platform steps