



Work platform folding, with double-sided access, Number of steps including platform: 2X3



Order data

Order number	966070 2X3
GTIN	4003866403738
Item class	96Z

Description

Version:

Treads and stiles of extruded aluminium profile.

Large platform with integrated hinged connection.

85 mm deep treads with anti-slip grooves and patented 7-point tread-stile connection. Optimum stability due to rigid connections on both sides.

Standard:

DIN EN 14183.

Technical description

Accessibility	double-sided
Platform height without railing	0.74 m
outer width at bottom	0.75 m
Working height approx.	2.74 m
Weight	7.9 kg

Number of steps including platform	2×3
Type of step	step
Platform depth	300 mm
Rung/step depth	85 mm
Platform width	600 mm
Ladders and platforms load capacity	150 kg
Type of product	Work platform