

**Platform steps, Number of steps including platform: 3****Order data**

Order number	966190 3
GTIN	4003866555215
Item class	96Z

Description**Version:**

Stiles made from high-strength extruded aluminium sections with screw channels for flexible assembly. The scope of supply excludes handrails and platform railings. These are available under No. 966196 and No. 966198. Steps rise angle 45°. Platform length 400 mm. Serrated aluminium tread covering. Fitted with rollers on the support section.

Standard:

DIN EN ISO 14 122

Technical description

Type of step	Step
Throat	1070 mm
Platform height without railing	0.6 m
Standard	DIN EN ISO 14 122
Platform length	400 mm
Material	Stiles of high-strength extruded aluminium profiles
Number of steps including platform	3

Step inclination	45 degrees
Weight	34 kg
Accessibility	single-sided
Rung/step width	600 mm
Rollers	yes
Ladders and platforms load capacity	300 kg
Product name attribute	Tread width 600 mm
Two hands free principle	yes
Type of product	Platform steps