



Stepladder single-sided access, Number of steps including platform: 6



Order data

Order number	966000 6
GTIN	4003866403363
Item class	96Z

Description

Version:

Treads and stiles made of extruded aluminium sections. Large safety platform (380 × 260 mm) with integrated hinged connection, **safety bridge** and wide **shelf**. Treads 85 mm deep with safe, non-slip serrated surfaces and patented 7-point connection between tread and stile. Optimum stability due to rigid connections on both sides. Two integral bucket hooks.

Standard:

DIN EN 131.

Technical description

Rung/step depth	85 mm
Storage tray available	yes
Cross beam height	87 mm
Platform height	1.35 m
Type of step	Step
Ladder length	2.13 m

Standard	DIN EN 131-2; TRBS 2121; BGI 694
Weight	9 kg
Material	Steps and stiles made of extruded aluminium sections
Number of steps including platform	6
Working height approx.	3.35 m
outer width at bottom	0.52 m
Accessibility	single-sided
Ladders and platforms load capacity	150 kg
Type of product	Stepladder