



Work platform folding, with double-sided access, Number of steps including platform: 2X4



Order data

Order number	966070 2X4
GTIN	4003866403745
Item class	96Z

Description

Version:

Treads and stiles of extruded aluminium profile.

Large platform with integrated hinged connection.

85 mm deep treads with anti-slip grooves and patented 7-point tread-stile connection. Optimum stability due to rigid connections on both sides.

Standard:

DIN EN 14183.

Ladders and platforms load capacity: 150 kg

Working height approx.: 2.99 m

Platform height without railing: 0.99 m

Platform width: 600 mm

Platform depth: 300 mm

outer width at bottom: 0.8 m

Weight: 10.3 kg

Technical description

Weight	10.3 kg
Platform width	600 mm
Accessibility	double-sided
Rung/step depth	85 mm
Working height approx.	2.99 m
Platform depth	300 mm
Type of step	step
Number of steps including platform	2×4
Platform height without railing	0.99 m
outer width at bottom	0.8 m
Ladders and platforms load capacity	150 kg
Type of product	Work platform