

Garant**General purpose basic rack, Depth 500 mm, Height: 3000mm****Order data**

Order number	990010 3000
GTIN	4045197518293
Item class	91I

Description**Version:**

Very sturdy square supports 40×40×2 mm, mountings at increments of 40: 40 mm with insertion slots for setting the storage shelves to the right height for the goods to be stored. Supports have plastic base plates. **Shelves with particularly high load capacity** of strong sheet metal with side faces bent inwards.

Bay load capacity: At 600 mm shelf spacing, maximum bay load 1375 – 5500 kg.

Application:

Ideal for industry, craft, trade, administration, archives etc. The sizes are designed to match commercially available metal and plastic storage containers for the best use of space. Can be set up as single, row or double rack. **Simple, quick, and exact installation, no bolts required**, the storage shelves are simply hinged and locked in place with the appropriate taper pins (No. 968420).

Colour:

Rack supports jet black RAL 9005, shelves grey **powder-coated**.

Note:

- **Storage boxes for mounting on the universal racking can be found in group 96.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Rack installation	Basic rack
Number of shelves	7
Shelf width	1000 mm
Rack height	3000 mm
Assembled size basic rack width	1058 mm
Customer assembly	yes
Storage shelf clear width	950 mm
Assembled size basic rack height	3004 mm
Number of rack stiles	4
Type of shelf fastening	Taper pins
maximum bay load at 600 mm shelf spacing	1375 - 5500 kg
Plug-in assembly	yes
Storage shelf depth	500 mm
Rack depth	500 mm
Shelf load capacity / maximum distributed shelf load (on metal)	180 kg
Height adjustment interval	40 mm
Product name attribute	Depth 500 mm
Type of product	Storage shelf

Accessories

Single storage shelf with 4 brackets and 4 pins Depth 500 mm	990060 500
Rack support with plastic base plate, piece Height 3000 mm	990050 3000
Wedges and taper pins set for general-purpose rack	968420