

**Platform steps, Number of steps including platform: 5****Order data**

Order number	966194 5
GTIN	4003866555314
Item class	96Z

**Description****Version:**

Stiles made from high-strength extruded aluminium sections with screw channels for flexible assembly. The scope of supply excludes handrails and platform railings. These are available under No. 966196 and No. 966198. Steps rise angle 45°. Platform length 400 mm. Serrated aluminium tread covering. Fitted with rollers on the support section.

**Standard:**

**DIN EN ISO 14 122**

**Technical description**

Number of steps including platform	5
Step inclination	45 degrees
Throat	1470 mm
Material	Stiles of high-strength extruded aluminium profiles
Weight	46 kg
Standard	DIN EN ISO 14 122
Platform length	400 mm

Type of step	Step
Platform height without railing	0.99 m
Accessibility	single-sided
Rung/step width	1000 mm
Rollers	yes
Ladders and platforms load capacity	300 kg
Product name attribute	Tread width 1000 mm
Two hands free principle	yes
Type of product	Platform steps