



Multi-purpose ladder 3-part, Number of rungs: 3X8



Order data

Order number	966120 3X8
GTIN	4003866415380
Item class	96Z

Description

Version:

Rungs and stiles made from extruded aluminium sections. Rung-stile connection by strong high quality flanging. High-strength perlon straps and an additional rigid connection prevent splay. Wrap-around stile guides (exchangeable). Upper ladder with parking hooks and lift-off retainer. Optimum stability due to extra wide crossbar base. Can be used on steps/stairs, the upper ladder can also be used as a separate lean-to ladder.

Standard:

DIN EN 131.

Technical description

Cross-span width	1 m
Type of step	Rung
Length as 2-part single ladder and as stepladder with extension piece	4.1 m
Number of steps	3×8

Standard	DIN EN 131-2
Weight	17.5 kg
Cross beam height	73 mm
Ladder parts length	2.45 m
Ladder length extended	5.8 m
Material	Rungs and stiles made of extruded aluminium sections
Max. working height as a 3-part lean-to ladder, approx.	6.65 m
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder