



Stepladder single-sided access, Number of steps including platform: 8



Order data

Order number	966000 8
GTIN	4003866403387
Item class	96Z

Description

Version:

Treads and stiles made of extruded aluminium sections. Large safety platform (380 × 260 mm) with integrated hinged connection, **safety bridge** and wide **shelf**. Treads 85 mm deep with safe, non-slip serrated surfaces and patented 7-point connection between tread and stile. Optimum stability due to rigid connections on both sides. Two integral bucket hooks.

Standard:

DIN EN 131.

Technical description

Material	Steps and stiles made of extruded aluminium sections
Working height approx.	3.75 m
Weight	13 kg
Type of step	Step
Ladder length	2.6 m

Storage tray available	yes
Standard	DIN EN 131-2; TRBS 2121; BGI 694
Cross beam height	87 mm
Rung/step depth	85 mm
Platform height	1.75 m
Number of steps including platform	8
outer width at bottom	0.56 m
Accessibility	single-sided
Ladders and platforms load capacity	150 kg
Type of product	Stepladder