




Work platform individual module, Type: D



Order data

Order number	966150 D
GTIN	4003866402632
Item class	96Z

Description

Version:

Extremely robust, torsion-resistant, corrosion-proof, and weatherproof aluminium alloy structure. Steps of serrated aluminium plate 555×250 mm.

Modular structure allows changes and extensions.

Add-on modules available for 4 different heights.

The two-step basic module with up to 3 add-on steps is suitable for mobile use. Add-on modules available from module type B.

Standard:

DIN EN 14183.

Technical description

Platform depth	0.8 m
Weight of module combination	9.2 kg
Standard	DIN EN 14183
Rung/step width	555 mm
Platform height without railing	0.6 m
Weight of individual module	4.4 kg

Working height	2.6 m
Type of step	Step
Material	Overall light alloy design; steps of ribbed aluminium plate.
Rung/step depth	250 mm
Module combination	B+D
Accessibility	single-sided
Number of steps including platform	3
Ladders and platforms load capacity	150 kg
Type of product	Work platform