



## Multi-purpose ladder 3-part, Number of rungs: 3X10



### Order data

Order number	966120 3X10
GTIN	4003866415403
Item class	96Z

### Description

#### Version:

Rungs and stiles made from extruded aluminium sections. Rung-stile connection by strong high quality flanging. High-strength perlon straps and an additional rigid connection prevent splay. Wrap-around stile guides (exchangeable). Upper ladder with parking hooks and lift-off retainer. Optimum stability due to extra wide crossbar base. Can be used on steps/stairs, the upper ladder can also be used as a separate lean-to ladder.

#### Standard:

**DIN EN 131.**

### Technical description

Type of step	Rung
Ladder length extended	6.9 m
Length as 2-part single ladder and as stepladder with extension piece	4.95 m
Number of steps	3×10

Cross-span width	1.1 m
Cross beam height	85 mm
Weight	23.3 kg
Ladder parts length	3 m
Standard	DIN EN 131-2
Material	Rungs and stiles made of extruded aluminium sections
Max. working height as a 3-part lean-to ladder, approx.	7.7 m
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder