



Stepladder single-sided access, Number of steps including platform: 10



Order data

Order number	966000 10
GTIN	4003866403400
Item class	96Z

Description

Version:

Treads and stiles made of extruded aluminium sections. Large safety platform (380 × 260 mm) with integrated hinged connection, **safety bridge** and wide **shelf**. Treads 85 mm deep with safe, non-slip serrated surfaces and patented 7-point connection between tread and stile. Optimum stability due to rigid connections on both sides. Two integral bucket hooks.

Standard:

DIN EN 131.

Technical description

Rung/step depth	85 mm
Number of steps including platform	10
Working height approx.	4.2 m
Type of step	Step
Material	Steps and stiles made of extruded aluminium sections

Standard	DIN EN 131-2; TRBS 2121; BGI 694
Platform height	2.2 m
Storage tray available	yes
Cross beam height	87 mm
Weight	14 kg
outer width at bottom	0.61 m
Ladder length	3.05 m
Accessibility	single-sided
Ladders and platforms load capacity	150 kg
Type of product	Stepladder