



Multi-purpose ladder 3-part, Number of rungs: 3X12



Order data

Order number	966120 3X12
GTIN	4003866415427
Item class	96Z

Description

Version:

Rungs and stiles made from extruded aluminium sections. Rung-stile connection by strong high quality flanging. High-strength perlon straps and an additional rigid connection prevent splay. Wrap-around stile guides (exchangeable). Upper ladder with parking hooks and lift-off retainer. Optimum stability due to extra wide crossbar base. The upper ladder cannot be lifted off and used as a separate lean-to ladder.

Standard:

DIN EN 131.

Technical description

Length as 2-part single ladder and as stepladder with extension piece	6.1 m
Standard	DIN EN 131-2
Ladder parts length	3.55 m
Cross beam height	98 mm

Weight	28.8 kg
Type of step	Rung
Number of steps	3×12
Ladder length extended	8.6 m
Cross-span width	1.2 m
Material	Rungs and stiles made of extruded aluminium sections
Max. working height as a 3-part lean-to ladder, approx.	9.35 m
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder