

## Garant

### General purpose basic rack, Depth 400 mm, Height: 2000mm



#### Order data

Order number	990000 2000
GTIN	4045197518071
Item class	91I

#### Description

##### Version:

**Very sturdy square supports** 40×40×2 mm, mountings at increments of 40: 40 mm with insertion slots for setting the storage shelves to the right height for the goods to be stored. Supports have plastic base plates. **Shelves with particularly high load capacity** of strong sheet metal with side faces bent inwards.

**Bay load capacity:** At 600 mm shelf spacing, maximum bay load 1375 – 5500 kg.

##### Application:

Ideal for industry, craft, trade, administration, archives etc. The sizes are designed to match commercially available metal and plastic storage containers – for the best use of space. Can be set up as single, row or double rack. **Simple, quick, and exact installation, no bolts required**, the storage shelves are simply hinged and locked in place with the appropriate taper pins (No. 968420).

##### Colour:

Rack supports jet black RAL 9005, shelves grey **powder-coated**.

##### Note:

- **Storage boxes for mounting on the universal racking can be found in group 96.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Storage shelf clear width	950 mm
Rack installation	Basic rack
Shelf width	1000 mm
Number of rack stiles	4
Customer assembly	yes
Assembled size basic rack width	1058 mm
Assembled size basic rack height	2004 mm
Number of shelves	5
maximum bay load at 600 mm shelf spacing	1375 - 5500 kg
Rack height	2000 mm
Type of shelf fastening	Taper pins
Plug-in assembly	yes
Storage shelf depth	400 mm
Rack depth	400 mm
Shelf load capacity / maximum distributed shelf load (on metal)	180 kg
Height adjustment interval	40 mm
Product name attribute	Depth 400 mm
Type of product	Storage shelf

## Accessories

Single storage shelf with 4 brackets and 4 pins Depth 400 mm	990060 400
Rack support with plastic base plate, piece Height 2000 mm	990050 2000
Wedges and taper pins set for general-purpose rack	968420