



Single ladder, Number of steps: 14



Order data

Order number	966080 14
GTIN	4003866403844
Item class	96Z

Description

Version:

Treads and stiles made of extruded aluminium sections.

Treads 85 mm deep with safe, non-slip serrated surfaces and patented 7-point tread-stile connection.

Especially light and easy to carry, with smooth stile surfaces that are comfortable to hold.

External width: 400 mm

Standard:

DIN EN 131.

Note:

To DIN EN 131 with crossbar base.

Technical description

Material	Steps and stiles made of extruded aluminium sections
Type of step	step
Standard	DIN EN 131-2

Working height approx.	4.35 m
Width	400 mm
Cross beam height	87 mm
Ladder length	3.42 m
Weight	11.4 kg
Number of steps	14
Rung/step depth	85 mm
Number of stabilising cross struts	1
Ladders and platforms load capacity	150 kg
Type of product	Lean-to ladder