

## Garant

### General purpose basic rack, Depth 600 mm, Height: 2000mm



#### Order data

Order number	990020 2000
GTIN	4045197518095
Item class	91I

#### Description

##### Version:

**Very sturdy square supports** 40×40×2 mm, mountings at increments of 40: 40 mm with insertion slots for setting the storage shelves to the right height for the goods to be stored. Supports have plastic base plates. **Shelves with particularly high load capacity** of strong sheet metal with side faces bent inwards.

**Bay load capacity:** At 600 mm shelf spacing, maximum bay load 1375 – 5500 kg.

##### Application:

Ideal for industry, craft, trade, administration, archives etc. The sizes are designed to match commercially available metal and plastic storage containers for the best use of space. Can be set up as single, row or double rack. **Simple, quick, and exact installation, no bolts required**, the storage shelves are simply hinged and locked in place with the appropriate taper pins (No. 968420).

##### Colour:

Rack supports jet black RAL 9005, shelves grey **powder-coated**.

##### Note:

- **Storage boxes for mounting on the universal racking can be found in group 96.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Assembled size basic rack width	1058 mm
Storage shelf clear width	950 mm
Customer assembly	yes
maximum bay load at 600 mm shelf spacing	1375 - 5500 kg
Type of shelf fastening	Taper pins
Number of shelves	5
Shelf width	1000 mm
Plug-in assembly	yes
Assembled size basic rack height	2004 mm
Number of rack stiles	4
Rack installation	Basic rack
Rack height	2000 mm
Storage shelf depth	600 mm
Rack depth	600 mm
Shelf load capacity / maximum distributed shelf load (on metal)	180 kg
Height adjustment interval	40 mm
Product name attribute	Depth 600 mm
Type of product	Storage shelf

## Accessories

Single storage shelf with 4 brackets and 4 pins Depth 600 mm	990060 600
Rack support with plastic base plate, piece Height 2000 mm	990050 2000
Wedges and taper pins set for general-purpose rack	968420