

**Platform steps, Number of steps including platform: 4****Order data**

Order number	966192 4
GTIN	4003866555260
Item class	96Z

Description**Version:**

Stiles made from high-strength extruded aluminium sections with screw channels for flexible assembly. The scope of supply excludes handrails and platform railings. These are available under No. 966196 and No. 966198. Steps rise angle 45°. Platform length 400 mm. Serrated aluminium tread covering. Fitted with rollers on the support section.

Standard:

DIN EN ISO 14 122

Technical description

Platform height without railing	0.8 m
Platform length	400 mm
Throat	1270 mm
Number of steps including platform	4
Step inclination	45 degrees
Type of step	Step
Weight	39 kg
Standard	DIN EN ISO 14 122

Material	Stiles of high-strength extruded aluminium profiles
Accessibility	single-sided
Rung/step width	800 mm
Rollers	yes
Ladders and platforms load capacity	300 kg
Product name attribute	Tread width 800 mm
Two hands free principle	yes
Type of product	Platform steps