



Platform steps, Tread width 800 mm, Number of steps including platform: 5



Order data

Order number	966192 5
GTIN	4003866555277
Item class	96Z

Description

Version:

Stiles made from high-strength extruded aluminium sections with screw channels for flexible assembly. The scope of supply excludes handrails and platform railings. These are available under No. 966196 and No. 966198. Steps rise angle 45°. Platform length 400 mm. Serrated aluminium tread covering. Fitted with rollers on the support section.

Standard:

DIN EN ISO 14 122

Ladders and platforms load capacity: 300 kg

Platform height without railing: 0.99 m

Throat: 1470 mm

Weight: 46 kg

Technical description

Material	Stiles of high-strength extruded aluminium profiles
Type of step	Step
Standard	DIN EN ISO 14 122
Platform height without railing	0.99 m
Throat	1470 mm

Weight	46 kg
Platform length	400 mm
Step inclination	45 °
Number of steps including platform	5
Accessibility	single-sided
Tread width	800 mm
Ladders and platforms load capacity	300 kg
Product name attribute	Tread width 800 mm
Two hands free principle	yes
Type of product	Platform steps