

Garant**General purpose extension rack, Depth 400 mm, Height: 2500mm****Order data**

Order number	990005 2500
GTIN	4045197518262
Item class	911

Description**Version:**

Very sturdy square supports 40×40×2 mm, mountings at increments of 40: 40 mm with insertion slots for setting the storage shelves to the right height for the goods to be stored. Supports have plastic base plates. **Shelves with particularly high load capacity** of strong sheet metal with side faces bent inwards.

Bay load capacity: At 600 mm shelf spacing, maximum bay load 1375 – 5500 kg.

Application:

Ideal for industry, craft, trade, administration, archives etc. The sizes are designed to match commercially available metal and plastic storage containers for the best use of space. Can be set up as single, row or double rack. **Simple, quick, and exact installation, no bolts required**, the storage shelves are simply hinged and locked in place with the appropriate taper pins (No. 968420).

Colour:

Rack supports jet black RAL 9005, shelves grey **powder-coated**.

Note:

- **Storage boxes for mounting on the universal racking can be found in group 96.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Assembled size add-on rack height	2504 mm
Customer assembly	yes
Rack installation	Extension rack
Shelf width	1000 mm
Assembled size add-on rack width	1031 mm
Storage shelf clear width	950 mm
Type of shelf fastening	Taper pins
maximum bay load at 600 mm shelf spacing	1375 - 5500 kg
Plug-in assembly	yes
Number of shelves	6
Number of rack stiles	2
Rack height	2500 mm
Storage shelf depth	400 mm
Rack depth	400 mm
Shelf load capacity / maximum distributed shelf load (on metal)	180 kg
Height adjustment interval	40 mm
Product name attribute	Depth 400 mm
Type of product	Storage shelf

Accessories

Single storage shelf with 4 brackets and 4 pins Depth 400 mm	990060 400
Rack support with plastic base plate, piece Height 2500 mm	990050 2500
Wedges and taper pins set for general-purpose rack	968420