

Garant

General purpose extension rack, Depth 600 mm, Height: 2500mm



Order data

| | |
|--------------|---------------|
| Order number | 990025 2500 |
| GTIN | 4045197518286 |
| Item class | 911 |

Description

Version:

Very sturdy square supports 40×40×2 mm, mountings at increments of 40: 40 mm with insertion slots for setting the storage shelves to the right height for the goods to be stored. Supports have plastic base plates. **Shelves with particularly high load capacity** of strong sheet metal with side faces bent inwards.

Bay load capacity: At 600 mm shelf spacing, maximum bay load 1375 – 5500 kg.

Application:

Ideal for industry, craft, trade, administration, archives etc. The sizes are designed to match commercially available metal and plastic storage containers for the best use of space. Can be set up as single, row or double rack. **Simple, quick, and exact installation, no bolts required**, the storage shelves are simply hinged and locked in place with the appropriate taper pins (No. 968420).

Colour:

Rack supports jet black RAL 9005, shelves grey **powder-coated**.

Note:

- **Storage boxes for mounting on the universal racking can be found in group 96.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|---|----------------|
| Number of shelves | 6 |
| maximum bay load at 600 mm shelf spacing | 1375 - 5500 kg |
| Assembled size add-on rack width | 1031 mm |
| Storage shelf clear width | 950 mm |
| Assembled size add-on rack height | 2504 mm |
| Rack height | 2500 mm |
| Number of rack stiles | 2 |
| Plug-in assembly | yes |
| Rack installation | Extension rack |
| Shelf width | 1000 mm |
| Type of shelf fastening | Taper pins |
| Customer assembly | yes |
| Storage shelf depth | 600 mm |
| Rack depth | 600 mm |
| Shelf load capacity / maximum distributed shelf load (on metal) | 180 kg |
| Height adjustment interval | 40 mm |
| Product name attribute | Depth 600 mm |
| Type of product | Storage shelf |

Accessories

| | |
|--|-------------|
| Single storage shelf with 4 brackets and 4 pins Depth 600 mm | 990060 600 |
| Rack support with plastic base plate, piece Height 2500 mm | 990050 2500 |
| Wedges and taper pins set for general-purpose rack | 968420 |