

Garant

Side panel complete with fastenings, set, Depth 500 mm, Height: 2500mm



Order data

Order number	990105 2500
GTIN	4045197518149
Item class	91I

Description

Version:

With □ 9×9 mm at 37 mm intervals for mounting hooks and supports, and perforated panel accessories. These can be found in Group 95. A side panel consists of two perforated panels mounted over one another. Supplied complete with fastenings.

Application:

For side closure at the end of a rack (not suitable as divider between two racks). To enclose a complete racking bay on the left- and right-hand side, 2 side panels must be ordered.

Colour:

Anthracite grey RAL 7016 **powder-coated.**

Technical description

suitable for storage shelf racking	yes
Can be used as a partition	no
Customer assembly	yes
Width	500 mm

Side panel extension	two-piece
suitable for racking height	2500 mm
suitable for racking depth	500 mm
Fastening materials supplied	yes
Application range	Storage shelf
Height	2500 mm
Hoffmann perforated panel grid interval	9×9 mm
Product name attribute	Depth 500 mm
Type of product	Side panel