



## Platform steps mobile, double-sided access, Number of steps including platform: 7



### Order data

Order number	966270 7
GTIN	4003866419852
Item class	96Z

### Description

#### Version:

Comfortable platform steps with 200 mm deep treads (60° rise angle). Spacious platform (600×800 mm) with platform railing (1.00 m high) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

#### Standard:

**DIN EN 131-7**

#### Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

### Technical description

Footprint depth	2.62 m
Platform height without railing	1.68 m
Platform width	600 mm
Rung/step depth	200 mm

Platform depth	800 mm
Number of castors with parking brake	2
Step inclination	60 degrees
Weight	57.5 kg
Standard	DIN EN 131-7
Accessibility	double-sided
Castors Ø	125 mm
Number of steps including platform	7
Number of castors without parking brake	2
with platform railings	yes
Footprint width	0.98 m
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps