



Platform steps mobile, single-sided access, Number of steps including platform: 6



Order data

Order number	966220 6
GTIN	4003866419746
Item class	96Z

Description

Version:

Comfortable platform steps with 200 mm deep treads (60° angle of inclination). Spacious platform (600×800 mm) with platform guardrail (at a height of 1.00 m) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

Standard:

DIN EN 131-7

Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

Technical description

Platform width	600 mm
Platform height without railing	1.44 m
Platform depth	800 mm
Accessibility	single-sided

Footprint depth	1.81 m
Step inclination	60 degrees
Castors Ø	125 mm
Rung/step depth	200 mm
Standard	DIN EN 131-7
Number of castors with parking brake	2
Number of steps including platform	6
Number of castors without parking brake	2
Footprint width	0.93 m
Weight	38.4 kg
with platform railings	yes
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps