



Safemaster S fold-away platform ladder, Number of steps including platform: 7



Order data

Order number	966275 7
GTIN	4003866416776
Item class	96Z

Description

Version:

Compact platform ladder with 80 mm deep rungs. Work platform (400×400 mm) with guard rails around 3 sides and storage tray. Optimum stability due to rigid locking bar on both sides.

Standard:

EN 131

Technical description

Weight	17.4 kg
Footprint width	0.74 m
Platform height without railing	1.85 m
Storage tray available	yes
Knee bar	no
Accessibility	single-sided
Platform width	400 mm
Rung/step depth	80 mm

Belt to prevent splay	double-sided, rigid connection
Footprint depth	1.6 m
Standard	EN 131
Handrail	2
Platform depth	400 mm
Number of steps including platform	7
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder