



## Platform steps mobile, single-sided access, Number of steps including platform: 7



### Order data

Order number	966220 7
GTIN	4003866419753
Item class	96Z

### Description

#### Version:

Comfortable platform steps with 200 mm deep treads (60° angle of inclination). Spacious platform (600×800 mm) with platform guardrail (at a height of 1.00 m) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

#### Standard:

**DIN EN 131-7**

#### Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

### Technical description

Platform depth	800 mm
with platform railings	yes
Standard	DIN EN 131-7
Number of castors with parking brake	2

Number of castors without parking brake	2
Castors Ø	125 mm
Accessibility	single-sided
Footprint width	0.98 m
Footprint depth	1.99 m
Platform width	600 mm
Number of steps including platform	7
Weight	41.8 kg
Platform height without railing	1.68 m
Step inclination	60 degrees
Rung/step depth	200 mm
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps