



Safemaster S fold-away platform ladder, Number of steps including platform: 8



Order data

Order number	966275 8
GTIN	4003866416783
Item class	96Z

Description

Version:

Compact platform ladder with 80 mm deep rungs. Work platform (400×400 mm) with guard rails around 3 sides and storage tray. Optimum stability due to rigid locking bar on both sides.

Standard:

EN 131

Technical description

Accessibility	single-sided
Platform depth	400 mm
Storage tray available	yes
Platform width	400 mm
Handrail	2
Footprint depth	1.75 m
Footprint width	0.77 m
Knee bar	no

Number of steps including platform	8
Belt to prevent splay	double-sided, rigid connection
Platform height without railing	2.11 m
Rung/step depth	80 mm
Standard	EN 131
Weight	19.1 kg
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder