

Frame type S610-N, Height: 3000 mm**Order data**

Order number	991270 3000
GTIN	2050001686282
Item class	96P

Description**Version:**

Frame profiles with framework stiffening. Solid base plates transmit the load to the floor.
Supplied with 4 floor anchors per frame.

Description:**Assembled size:****Overall length of the rack::**

For frame stiles S610-N and S620-N: Nominal length + number of stiles×86 mm.

For frame stiles S625-N and S635-N: Nominal length + number of stiles×110 mm.

Suitable for :

Pallet racking up to build year 07/2018.

Colour:

Similar to RAL 5017 traffic blue, **powder-coated**.

Note:

The load capacities required for the racking bay determine the frame type. See load table for details.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Depth: 800 mm

Technical description

Depth	800 mm
Frame profile type	S610-N
Height	3000 mm