



Safemaster S fold-away platform ladder, Number of steps including platform: 9



Order data

Order number	966275 9
GTIN	4003866416790
Item class	96Z

Description

Version:

Compact platform ladder with 80 mm deep rungs. Work platform (400×400 mm) with guard rails around 3 sides and storage tray. Optimum stability due to rigid locking bar on both sides.

Standard:

EN 131

Technical description

Handrail	2
Footprint width	0.8 m
Platform width	400 mm
Weight	20.4 kg
Standard	EN 131
Platform height without railing	2.34 m
Accessibility	single-sided
Footprint depth	1.93 m

Storage tray available	yes
Belt to prevent splay	double-sided, rigid connection
Number of steps including platform	9
Platform depth	400 mm
Knee bar	no
Rung/step depth	80 mm
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder