



Folding platform, standard version, Platform height: 900/B mm



Order data

Order number	966310 900/B
GTIN	4003866537617
Item class	96Y

Description

Version:

Frame width 0.68 m;

Frame length 1.80 m.

Can be extended using standard parts.

Folding base module for quick assembly / disassembly.

Minimal space required for transport and storage.

Roller castors \varnothing 125 mm, with pins (not height-adjustable). Platform **with** step-through flap.

Description:

Range Z 600 / Z 500

Feature:

Range Z 600 / Z 500

Standard:

DIN EN 1004

Ladders and platforms load capacity: 200 kg

Working height approx.: 2.9 m

Scaffolding height: 1.9 m

Weight: 33.8 kg

Technical description

Platform height	900 mm
Platform version	with step-through flap
Castors Ø	125 mm
Weight	33.8 kg
Scaffolding length	1.8 m
Scaffolding height	1.9 m
Scaffolding width	0.68 m
Working height approx.	2.9 m
Norm	DIN EN 1004
Ladders and platforms load capacity	200 kg