



Telescopic platform ladder, Number of steps including platform: 5



Order data

| | |
|--------------|---------------|
| Order number | 966285 5 |
| GTIN | 4003866413256 |
| Item class | 96Z |

Description

Version:

Stand platform size 665×440 mm, with railing and knee bar. Easy adjustment of height using the sliding ladder principle.

With swing-out stabilisers. Two running wheels allow the ladder to be moved easily, even when fully extended.

Handrails and guard rails are automatically unfolded on set-up.

Standard:

EN 131.

Technical description

| | |
|------------------------------------|--------|
| Number of wheels | 2 |
| Standard | EN 131 |
| Number of steps including platform | 5 |
| Platform width | 440 mm |
| Knee bar | yes |

| | |
|---|----------------------|
| Stabiliser length (retracted) | 1 m |
| Weight | 28 kg |
| Platform depth | 665 mm |
| Platform height without railings inserted | 0.81 / 1.08 / 1.34 m |
| Stabiliser length (extended) | 1 m |
| Accessibility | single-sided |
| Handrail | 2 |
| Stabiliser width (extended) | 1.45 m |
| Stabiliser width (retracted) | 1.45 m |
| Ladders and platforms load capacity | 150 kg |
| Two hands free principle | yes |
| Safer Step | yes |
| Type of product | Platform ladder |