



## Telescopic platform ladder, Number of steps including platform: 7



### Order data

Order number	966285 7
GTIN	4003866413263
Item class	96Z

### Description

**Version:**

Stand platform size 665×440 mm, with railing and knee bar. Easy adjustment of height using the sliding ladder principle.

With swing-out stabilisers. Two running wheels allow the ladder to be moved easily, even when fully extended.

Handrails and guard rails are automatically unfolded on set-up.

**Standard:**

**EN 131.**

### Technical description

Accessibility	single-sided
Number of steps including platform	7
Stabiliser length (retracted)	0.81 m
Platform depth	665 mm
Stabiliser length (extended)	2.25 m

Knee bar	yes
Number of wheels	2
Stabiliser width (retracted)	1.8 m
Standard	EN 131
Platform height without railings inserted	1.05 / 1.30 / 1.60 / 1.83 m
Handrail	2
Platform width	440 mm
Stabiliser width (extended)	1.8 m
Weight	34 kg
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder