



## Stepladder with platform, single-sided access, Number of steps including platform: 6



### Order data

Order number	966272 6
GTIN	4003866404773
Item class	96Z

### Description

#### Version:

Stepladder with flanged steps 80 mm deep. Large working platform with aluminium chequer plate covering (380×390 mm). Aluminium storage tray. 2 handrails as standard, for safe ascent and descent. Optimum stability due to 2 high-strength perlon belts that prevent splay (from 5 treads).

#### Standard:

EN 131.

### Technical description

Number of steps including platform	6
outer width at bottom	0.68 m
Standard	EN 131
Storage tray available	yes
Rung/step depth	80 mm

Working height approx.	3.55 m
Platform width	380 mm
Handrail	2
Belt to prevent splay	2 high-strength Perlon belts
Platform depth	390 mm
Platform height without railing	1.55 m
Accessibility	single-sided
Weight	14 kg
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder