

Garant**Soft-faced hammer with rubber inserts, black, Housing Ø / material: 80Gmm****Order data**

Order number	752500 80G
GTIN	4045197992291
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Technical description

Head length with inserts	175 mm
Overall length	500 mm
Handle length	400 mm
Striking face Ø of the inserts	80 mm
Weight without inserts	1895 g
Colour	black
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

Accessories

Hickory hammer handle for body Ø 80 mm

752530 80

Nylon insert, hard for soft-faced hammer 80

752560 80

Rubber insert, soft for soft-faced hammer 80

752540 80