



Telescopic platform ladder, Number of steps including platform: 9



Order data

Order number	966285 9
GTIN	4003866413270
Item class	96Z

Description

Version:

Stand platform size 665×440 mm, with railing and knee bar. Easy adjustment of height using the sliding ladder principle.

With swing-out stabilisers. Two running wheels allow the ladder to be moved easily, even when fully extended.

Handrails and guard rails are automatically unfolded on set-up.

Standard:

EN 131.

Technical description

Platform depth	665 mm
Number of steps including platform	9
Handrail	2
Standard	EN 131
Stabiliser length (retracted)	0.81 m

Accessibility	single-sided
Stabiliser length (extended)	2.55 m
Stabiliser width (extended)	2.2 m
Stabiliser width (retracted)	2.2 m
Knee bar	yes
Weight	38.5 kg
Platform width	440 mm
Platform height without railings inserted	1.31 / 1.60 / 1.80 / 2.10 / 2.35 m
Number of wheels	2
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder