



## Folding platform, standard version, Platform height: 3700 mm



### Order data

Order number	966310 3700
GTIN	4003866537648
Item class	96Y

### Description

#### Version:

Frame width 0.68 m;

Frame length 1.80 m.

Can be extended using standard parts.

Folding base module for quick assembly / disassembly.

Minimal space required for transport and storage.

Roller castors Ø 125 mm, with pins (not height-adjustable). Platform **with** step-through flap.

#### Description:

**Range Z 600 / Z 500**

#### Feature:

**Range Z 600 / Z 500**

#### Standard:

**DIN EN 1004**

Ladders and platforms load capacity: 200 kg

Working height approx.: 5.7 m

Scaffolding height: 4.75 m

Weight: 96.1 kg

### Technical description

Weight	96.1 kg
Scaffolding width	0.68 m
Scaffolding length	1.8 m
Norm	DIN EN 1004
Working height approx.	5.7 m
Castors Ø	125 mm
Platform height	3700 mm
Platform version	with step-through flap
Scaffolding height	4.75 m
Ladders and platforms load capacity	200 kg