



Platform steps mobile, double-sided access, Number of steps including platform: 3



Order data

Order number	966270 3
GTIN	4003866419814
Item class	96Z

Description

Version:

Comfortable platform steps with 200 mm deep treads (60° rise angle). Spacious platform (600×800 mm) with platform railing (1.00 m high) and bars at foot and knee levels. Four sprung castors Ø 125 mm (2 with parking brakes).

Standard:

DIN EN 131-7

Note:

- **Handrail not included. Please order as additional item No. 966225.**
- **Delivered as components for easy self-assembly. Delivered unassembled.**

Technical description

Platform height without railing	0.72 m
Footprint depth	1.51 m
Number of steps including platform	3
Number of castors with parking brake	2

with platform railings	yes
Weight	31 kg
Castors Ø	125 mm
Platform depth	800 mm
Number of castors without parking brake	2
Platform width	600 mm
Footprint width	0.77 m
Accessibility	double-sided
Standard	DIN EN 131-7
Step inclination	60 degrees
Rung/step depth	200 mm
Type of step	Step
Knee bar	yes
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Type of product	Platform steps