



Telescopic platform ladder, Number of steps including platform: 12



Order data

Order number	966285 12
GTIN	4003866413287
Item class	96Z

Description

Version:

Stand platform size 665×440 mm, with railing and knee bar. Easy adjustment of height using the sliding ladder principle.

With swing-out stabilisers. Two running wheels allow the ladder to be moved easily, even when fully extended.

Handrails and guard rails are automatically unfolded on set-up.

Standard:

EN 131.

Technical description

Accessibility	single-sided
Knee bar	yes
Stabiliser length (extended)	2.5 m
Number of steps including platform	12
Number of wheels	2

Platform height without railings inserted	1.83 / 2.12 / 2.38 / 2.65 / 2.90 / 3.15 m
Handrail	2
Weight	50 kg
Platform depth	665 mm
Stabiliser width (extended)	2.8 m
Standard	EN 131
Stabiliser width (retracted)	2.8 m
Platform width	440 mm
Stabiliser length (retracted)	0.81 m
Ladders and platforms load capacity	150 kg
Two hands free principle	yes
Safer Step	yes
Type of product	Platform ladder